



16202069

**Rocker imprinted symbol for bell, R.1/R.3, p. white glossy**

**Technical Features**

**Architecture**

|                           |               |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

**Materials**

|                |               |
|----------------|---------------|
| Colour         | Polar white   |
| RAL code       | 9010          |
| Surface finish | Glossy        |
| Material       | Thermoplastic |
| Treatment      | Untreated     |

**Dimensions**

|        |          |
|--------|----------|
| Height | 57.80 mm |
| Width  | 57.80 mm |
| Depth  | 20 mm    |

**Connectivity**

|               |                |
|---------------|----------------|
| Mounting type | Clamp mounting |
|---------------|----------------|

**Equipment**

|                                |    |
|--------------------------------|----|
| Monitoring window/light outlet | No |
|--------------------------------|----|

**Accessories**

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP44 |
| Impact resistance IK          | IK05 |

**Texts**

|                                  |   |
|----------------------------------|---|
| Imprint                          | With imprinted symbol bell  |
| Installation mode                | Clamp fastening   |
| Push button                      | Also for KNX applications: push-button, 1-gang, and group push-button, 1-gang |
| Rocker switch/rocker push-button | For rocker push-buttons<br>For change-over/intermediate switch                |

**Suitable for**

|     |  |
|-----|--|
| R.x |  |
|-----|--|

**Sustainability**

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |