



16226089

**Rocker imprint "0", Q.x, p. white velvety**

**Technical Features**

**Architecture**

Control/operation element	Single rocker
---------------------------	---------------

**Materials**

Colour	Polar white
RAL code	9010
Surface finish	Velvety
Material	Duroplastic
Treatment	Untreated

**Dimensions**

Height	58 mm
Width	58 mm
Depth	22.50 mm

**Connectivity**

Mounting type	Clamp mounting
---------------	----------------

**Equipment**

Monitoring window/light outlet	No
--------------------------------	----

**Accessories**

Has labelling field	No
---------------------	----

**Safety**

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02
Usable in higher IP class	IP44 in combination with sealing set

**Texts**

Imprint	With imprint "0"
Installation mode	Clamp fastening
Rocker switch/rocker push-button	For multi-pole rocker switches

**Suitable for**

Q.x	
-----	--

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes