



TXM632C



OUTPUT DEVICE FOR 12 SHUTTERS / BLINDS 230V~ 4A / NE

Technical Features

Settings

Supported configuration mode	ETS easy
------------------------------	-------------

Connectivity

With bus system KNX radio	No
---------------------------	----

Installation, mounting

Mounting on	DIN rail
-------------	----------

Materials

Colour	Light grey
--------	------------

Equipment

With switch for manual switch	Yes
-------------------------------	-----

Electric current

Rated current	4 A
Max. switching current	4 A

Voltage

Operating voltage over bus	21 - 32 V
----------------------------	-----------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Connection

Cross-section flexible conductor	0.5 - 6 mm ²
Cross-section rigid conductor	0.5 - 6 mm ²

Capacity

Number of modules	10
-------------------	----

Texts

Function	With safety functions e.g. for wind, rain, alarm With positioning function for blind and lamella position With sun shade function
Type of connection	With screw terminals
Operating mode	Operating mode can be set for roller shutter/awning

Sustainability

RoHS conform	Yes
--------------	-----