



29511404



LED signal light, RGB, B.7, al., matt, lacq.

Technical Features

Voltage

| | |
|---------------|-------|
| Rated voltage | 230 V |
|---------------|-------|

Power

| | |
|----------------|-----|
| Power absorbed | 2 W |
|----------------|-----|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Lighting

| | |
|--------------|-----|
| Type of lamp | LED |
|--------------|-----|

Materials

| | |
|----------------|------------------|
| Colour | Aluminium |
| RAL code | 9006 |
| Surface finish | Matt |
| Material | Metal Plastic |
| Treatment | Varnished |

Dimensions

| | |
|--------|-------|
| Height | 70 mm |
| Width | 70 mm |
| Depth | 50 mm |

Connection

| | |
|-------------------------|-----------------------------|
| Conductor cross-section | 2.50 - 2.50 mm ² |
|-------------------------|-----------------------------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Texts

| | |
|-----------|--|
| Lighting | Light colours cold white, warm white, blue, orange, red, green, purple (magenta) and colour sequence callable via push-button Colour sequence can be stopped at any position via the push-button. |
| Labelling | Foils with imprint of symbols insertable |
| Imprint | Without imprint |