



JK216EG

**JK2 32 Module DIN Rail Box Glazed**

**Technical Features**

**Installation, mounting**

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | No               |
| Mounting on                | Surface mounting |

**Equipment**

|                            |     |
|----------------------------|-----|
| Number of rails            | 2   |
| Number of rows             | 2   |
| Number of section in width | 1   |
| With lock                  | Yes |
| Has neutral terminal block | Yes |

**Capacity**

|                   |    |
|-------------------|----|
| Number of modules | 32 |
|-------------------|----|

**Dimensions**

|        |           |
|--------|-----------|
| Height | 450 mm    |
| Width  | 465 mm    |
| Depth  | 165.50 mm |

**Cover, door**

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
|-------------------------|---|

**Dimensions**

|                       |    |
|-----------------------|----|
| Number of width units | 32 |
|-----------------------|----|

**Cover, door**

|                           |     |
|---------------------------|-----|
| Door/cover is transparent | Yes |
|---------------------------|-----|

**Materials**

|          |            |
|----------|------------|
| Material | Steel      |
| RAL code | 7035       |
| Colour   | Light grey |

**Equipment**

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
|-----------------------------|-----|

**Safety**

|                               |                               |
|-------------------------------|-------------------------------|
| Protection class              | Isolation class III           |
| Impact resistance IK          | IK05                          |
| Ingress Protection (IP) class | IP3X                          |
| Locking type                  | Key lock<br>Quarter turn lock |

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |