



WGDL111NP-12V

**12V 1G press switch with led**

**Technical Features**

**Electric current**

Switching current	10 A
-------------------	------

**Voltage**

Rated voltage	250 V
---------------	-------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Architecture**

Control/operation element	Single rocker
Number of poles	1

**Power**

Fluorescent lamps in duo circuit	0 W
----------------------------------	-----

**Materials**

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated
Transparent	No

**Dimensions**

Height	22 mm
Width	90 mm
Depth	25 mm
Built-in depth	25 mm

**Installation, mounting**

Mounting on	Wall mounting
-------------	---------------

**Controls and indicators**

Number of buttons	1
-------------------	---

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Connection**

Connector/plug type	British Standard
---------------------	------------------

**Safety**

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

**Accessories**

Has labelling field	No
---------------------	----

**Texts**

Switch mode	1-way
-------------	-------

**Suitable for**

shark	
-------	--

**Sustainability**

RoHS conform	Yes
--------------	-----