



TXA306



### Binary input 6 fold, universal, modular, KNX

#### Technical Features

##### Architecture

Bus system	EIB
------------	-----

##### Settings

Supported configuration mode	ETS easy
------------------------------	-------------

##### Electric current

Number of entry circuits	6
--------------------------	---

##### Equipment

External signal voltage necessary	No
-----------------------------------	----

##### Connectivity

With bus system KNX radio	No
---------------------------	----

##### Equipment

Radio frequency bidirectional	No
With battery	No
With HVAC control	No

##### Installation, mounting

Mounting on	DIN rail
-------------	----------

##### Lighting

LED controlling	No
-----------------	----

##### Materials

Material	Plastic
Colour	Light grey
RAL code	7035

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Use conditions

Operating temperature	0 - 45 °C
-----------------------	-----------

##### Voltage

Input voltage	24 - 230 V
Operating voltage over bus	21 - 32 V
Type voltage supply	AC/DC

##### Dimensions

Length	70 mm
Height	90 mm
Depth	60 mm

##### Texts

Type of connection	With quickconnect plug-in terminals
--------------------	-------------------------------------

##### Sustainability

RoHS conform	Yes
--------------	-----