



ERD418S

Humfree Relay 16A, 2NO+2NC, 24V~ 50/60Hz

Technical Features

Connection

Type of contacts	2NC+2NO
------------------	---------

Electric current

Rated current	16 A
---------------	------

Capacity

Number of modules	2
-------------------	---

Frequency

Frequency	50 - 50 Hz
-----------	------------

Voltage

Rated impulse withstand voltage Uimp	4000 V
Rated insulation voltage Ui	440 V
Rated operational voltage Ue	400 - 400 V
Command voltage AC	24 - 24 V
Command voltage DC	0 - 0 V

Use conditions

Operating temperature	-10 - 50 °C
-----------------------	-------------

Use

Category of use	AC-7a/AC-7b
-----------------	-------------

Use conditions

Storage/transport temperature	-40 - 80 °C
-------------------------------	-------------

Endurance

Number of mechanical operations	100000
---------------------------------	--------

Texts

Safety hint	Humfree contactors are not suitable for intensive use cases (powered 24/7) and in these cases industrial contactors must be used.
-------------	---

Endurance

Electric endurance in number of cycles	30000
--	-------

Power

Total power loss under IN	4.80 W
Inrush power absorbed	2.80 VA

Dimensions

Height	83 mm
Width	35.75 mm
Depth	60 mm

Connection

Number of contacts	4
--------------------	---

Equipment

Number of NO contacts	2
Number of NC contacts	2
With switch for manual switch	Yes

Connection

Cross-section flexible conductor	1 - 6 mm ²
Cross-section rigid conductor	1 - 10 mm ²

Installation, mounting

Nominal tightening torque	1.20 - 1.20 Nm
---------------------------	----------------

Architecture	
Number of poles	4
Sustainability	
RoHS conform	Yes