Product Datasheet
41357003

41357003

SCHUKO soc.out., enhncd contact prot., screw-in lift term., K.5, al. anodised

Technical Features

Voltage	
Rated voltage	250 V
Electric current	
Rated current	16 A
Frequency	
Frequency	50 - 60 Hz
Materials	
Colour	Aluminium
RAL code	9006
Surface finish	Matt
Material	Aluminium
Treatment	Anodised
Dimensions	
Height	71 mm
Width	71 mm
Number of units	1
Built-in depth flush-mounted boxes	31 mm
Built-in depth	32 mm
Installation, mounting	
Mounting on	Flush mounting
Connectivity	
Type of connection	Screw terminal
Mounting type	Screw mounting Claw mounting
Equipment	
Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No
Accessories	
Has labelling field	No
Capacity	
Number of modules	1
Safety	
With enhanced contact protection	Yes
Impact resistance IK	IK07
Ingress Protection (IP) class	IP20
Functions	
With orientation lighting	No
With function lighting	No
Identification	
With imprint	No

Texts	
Cover	Central cover plate
Protection	Enhanced contact protection
Type of connection	With screw-in lift terminals

Suitable for
K.x

Sustainability	
Halogen free	Yes
RoHS conform	Yes