Product Datasheet
BD241N

BD241N

Earth leakage add-on block 2P 40A 30mA AC Class

Technical Features

Architecture

Neutral position	Right
Number of poles	2

Capacity

Number of modules	2

Voltage

Rated operational voltage Ue	230 - 230 V
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

Frequency

Frequency	50 - 50 Hz

Electric current

Rated residual operating current Idn	30 mA
Rated current	40 A

Connectivity

Down connection alignment for modular devices	Aligned terminal

Installation, mounting

Nominal tightening torque	2.90 - 2.90 Nm
Nominal tightening torque down terminal	2.90 - 2.90 Nm

Dimensions

Height	70 mm
Width	44 mm
Depth	92 mm