



WXF462N

Socket Israel night

Technical Features

Electric current

Rated current	16 A
---------------	------

Use conditions

Operating temperature	-10 - 35 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Jet black
RAL code	9005
Surface finish	Satin finish
Material	Polycarbonate (PC)

Dimensions

Height	45 mm
Width	45 mm
Depth	37 mm
Built-in depth flush-mounted boxes	37 mm

Connectivity

Type of connection	Screw terminal
Mounting type	Click mounting

Equipment

Connector/plug type socket outlet	Israel socket outlet
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	2
-------------------	---

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK05
Ingress Protection (IP) class	IP21

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Protection	Enhanced contact protection
------------	-----------------------------

Suitable for

gallery	
---------	--

Sustainability

REACH-SVHC free	Yes
-----------------	-----