



WXF462R

Socket Israel red

Technical Features

Electric current

Rated current	16 A
---------------	------

Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

Use conditions

Operating temperature	-10 - 35 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Red
RAL code	3020
Surface finish	Satin finish
Material	Polycarbonate (PC)

Dimensions

Height	45 mm
Width	45 mm
Depth	37 mm
Built-in depth flush-mounted boxes	37 mm

Connectivity

Type of connection	Screw terminal
Mounting type	Click mounting

Equipment

Connector/plug type socket outlet	Israel socket outlet
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	2
-------------------	---

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK05
Ingress Protection (IP) class	IP21

Functions

With orientation lighting	No
With function lighting	No

Texts

Imprint	Without imprint
Protection	Enhanced contact protection

Suitable for

gallery	
---------	--

Sustainability

REACH-SVHC free	Yes
-----------------	-----