



WXD003N

Rocker VMC gallery 2 modules night

Technical Features

Architecture

Control/operation element	Single push button
---------------------------	--------------------

Controls and indicators

Number of buttons	1
-------------------	---

Materials

Colour	Jet black
RAL code	9005
Surface finish	Satin finish
Material	Polycarbonate (PC)
Treatment	Varnished

Dimensions

Height	44.60 mm
Width	44.70 mm
Depth	8 mm

Capacity

Number of modules	2
-------------------	---

Connectivity

Mounting type	Click mounting
---------------	----------------

Equipment

Monitoring window/light outlet	No
--------------------------------	----

Accessories

Has labelling field	No
---------------------	----

Safety

Ingress Protection (IP) class	IP21
Impact resistance IK	IK05

Use conditions

Operating temperature	-10 - 35 °C
-----------------------	-------------

Texts

Imprint	Symbol "rotational speed"
---------	---------------------------

Suitable for

gallery	
---------	--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes