



WXD003N

**Rocker VMC gallery 2 modules night**

**Technical Features**

**Architecture**

Control/operation element	Single push button
---------------------------	--------------------

**Controls and indicators**

Number of buttons	1
-------------------	---

**Materials**

Colour	Jet black
RAL code	9005
Surface finish	Satin finish
Material	Polycarbonate (PC)
Treatment	Varnished

**Dimensions**

Height	44.60 mm
Width	44.70 mm
Depth	8 mm

**Capacity**

Number of modules	2
-------------------	---

**Connectivity**

Mounting type	Click mounting
---------------	----------------

**Equipment**

Monitoring window/light outlet	No
--------------------------------	----

**Accessories**

Has labelling field	No
---------------------	----

**Safety**

Ingress Protection (IP) class	IP21
Impact resistance IK	IK05

**Use conditions**

Operating temperature	-10 - 35 °C
-----------------------	-------------

**Texts**

Imprint	Symbol "rotational speed"
---------	---------------------------

**Suitable for**

gallery	
---------	--

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes