



WMSSU83FO

### 13A FCU Switched with Flex Outlet

#### Technical Features

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Materials

Colour	White
--------	-------

Surface finish	Glossy
----------------	--------

Material	Urea formaldehyde
----------	-------------------

Treatment	Untreated
-----------	-----------

#### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Controls and indicators

Number of buttons	1
-------------------	---

#### Dimensions

Dimensions	86 x 86 mm
------------	------------

Built-in depth	25.30 mm
----------------	----------

Built-in depth flush-mounted boxes	25 mm
------------------------------------	-------

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Electric current

Rated current	13 A
---------------	------

#### Texts

Installation mode	For flush-mounted and hollow wall mounting
-------------------	--

Lighting	Without lighting (cannot be illuminated)
----------	--

Switch mode	2-pole
-------------	--------

#### Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----