



WXD003D

### Rocker VMC gallery 2 modules dune

#### Technical Features

##### Architecture

Control/operation element	Single push button
---------------------------	--------------------

##### Controls and indicators

Number of buttons	1
-------------------	---

##### Materials

Colour	White
RAL code	1013
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated

##### Dimensions

Height	8 mm
Depth	8 mm

##### Capacity

Number of modules	2
-------------------	---

##### Connectivity

Mounting type	Click mounting
---------------	----------------

##### Equipment

Monitoring window/light outlet	No
--------------------------------	----

##### Accessories

Has labelling field	No
---------------------	----

##### Safety

Ingress Protection (IP) class	IP21
Impact resistance IK	IK05

##### Use conditions

Operating temperature	-10 - 35 °C
-----------------------	-------------

##### Texts

Imprint	Symbol "rotational speed"
---------	---------------------------

##### Suitable for

gallery	
---------	--

##### Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes