



WXD003B

Rocker VMC gallery 2 modules pure-white

Technical Features

Architecture

| | |
|---------------------------|--------------------|
| Control/operation element | Single push button |
|---------------------------|--------------------|

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

Materials

| | |
|----------------|--------------------|
| Colour | Traffic white |
| RAL code | 9016 |
| Surface finish | Glossy |
| Material | Polycarbonate (PC) |
| Treatment | Untreated |

Dimensions

| | |
|--------|----------|
| Height | 44.60 mm |
| Width | 44.70 mm |
| Depth | 8 mm |

Capacity

| | |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

Connectivity

| | |
|---------------|----------------|
| Mounting type | Click mounting |
|---------------|----------------|

Equipment

| | |
|--------------------------------|----|
| Monitoring window/light outlet | No |
|--------------------------------|----|

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP21 |
| Impact resistance IK | IK05 |

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10 - 35 °C |
|-----------------------|-------------|

Texts

| | |
|---------|---------------------------|
| Imprint | Symbol "rotational speed" |
|---------|---------------------------|

Suitable for

| | |
|---------|--|
| gallery | |
|---------|--|

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |