



HHA040U

### Moulded Case Circuit Breaker h3 x160 TM ADJ 3P3D 40A 25kA CTC

#### Technical Features

##### Electric current

Rated current	40 A
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 400 V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 240 V AC IEC 60947-2	35 kA
Rated service breaking capacity I <sub>cs</sub> under 230 V AC according to IEC 60947-2	25 kA

##### Architecture

Number of poles	3
-----------------	---

##### Electric current

Rated service breaking capacity I <sub>cs</sub> under 400 V AC according to IEC 60947-2	20 kA
---	-------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Voltage

Rated impulse withstand voltage U <sub>imp</sub>	8000 V
Rated insulation voltage U <sub>i</sub>	690 V
Rated operational voltage U <sub>e</sub>	220 - 415 V

##### Functions

Trip unit	TM A/F
-----------	--------

##### Power

Total power loss under I <sub>N</sub>	11 W
---------------------------------------	------

##### Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

##### Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

##### Connection

Cross-section flexible conductor	4 - 70 mm <sup>2</sup>
Cross-section rigid conductor	4 - 95 mm <sup>2</sup>

##### Connectivity

Type of connection	Screw terminal
--------------------	----------------

##### Settings

Thermal protection knob setting xI <sub>N</sub>	0,63 0,8 1
---	------------------

##### Dimensions

Height	130 mm
Width	75 mm
Depth	68 mm

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes