



WXD004D

**Rocker for switch gallery 0-1 marking 2 modules dune**

**Technical Features**

**Architecture**

Control/operation element	Single push button
---------------------------	--------------------

**Controls and indicators**

Number of buttons	1
-------------------	---

**Materials**

Colour	White
RAL code	1013
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated

**Dimensions**

Height	44.60 mm
Depth	8 mm

**Capacity**

Number of modules	2
-------------------	---

**Connectivity**

Mounting type	Click mounting
---------------	----------------

**Equipment**

Monitoring window/light outlet	No
--------------------------------	----

**Accessories**

Has labelling field	No
---------------------	----

**Safety**

Ingress Protection (IP) class	IP21
Impact resistance IK	IK05

**Use conditions**

Operating temperature	-10 - 35 °C
-----------------------	-------------

**Texts**

Imprint	With imprint "0 - 1"
---------	----------------------

**Suitable for**  
gallery

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes