



WBSP2SUSBAC-MB

## SIL. Twin Socket + USB A+C MB

### Technical Features

#### Electric current

Rated current	10 A
---------------	------

#### Voltage

Nominal voltage	230 - 230 V
-----------------	-------------

#### Frequency

Frequency	50 - 50 Hz
-----------	------------

#### Materials

Colour	Black
Surface finish	Matt
Material	Polycarbonate (PC)

#### Dimensions

Height	82 mm
Width	120 mm
Depth	50.80 mm
Built-in depth flush-mounted boxes	70 mm

#### Connection

Connector/plug type	Screw terminal
---------------------	----------------

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Connectivity

Mounting type	Screw mounting
Connector/plug type USB	AC

#### Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

#### Safety

Impact resistance IK	IK08
Ingress Protection (IP) class	IP20

#### Functions

With orientation lighting	No
---------------------------	----

#### Texts

Imprint	Without imprint
Cover	Full cover plate
Protection	Yes

#### Suitable for

silhouette	
------------	--

#### Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes