



ETC325

### Night & Day Contactor 25A, 3NO, 230V~50Hz

#### Technical Features

##### Connection

|                  |     |
|------------------|-----|
| Type of contacts | 3NO |
|------------------|-----|

##### Electric current

|               |      |
|---------------|------|
| Rated current | 25 A |
|---------------|------|

##### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

##### Voltage

|                                      |             |
|--------------------------------------|-------------|
| Rated impulse withstand voltage Uimp | 4000 V      |
| Rated insulation voltage Ui          | 440 V       |
| Rated operational voltage Ue         | 400 - 400 V |
| Command voltage AC                   | 230 - 230 V |
| Command voltage DC                   | 0 - 0 V     |

##### Use conditions

|                       |             |
|-----------------------|-------------|
| Operating temperature | -10 - 50 °C |
|-----------------------|-------------|

##### Use

|                 |             |
|-----------------|-------------|
| Category of use | AC-7a/AC-7b |
|-----------------|-------------|

##### Use conditions

|                               |             |
|-------------------------------|-------------|
| Storage/transport temperature | -40 - 80 °C |
|-------------------------------|-------------|

##### Endurance

|                                        |        |
|----------------------------------------|--------|
| Number of mechanical operations        | 100000 |
| Electric endurance in number of cycles | 30000  |

##### Power

|                           |       |
|---------------------------|-------|
| Total power loss under IN | 6 W   |
| Inrush power absorbed     | 21 VA |

##### Dimensions

|        |          |
|--------|----------|
| Height | 83 mm    |
| Width  | 35.75 mm |
| Depth  | 64 mm    |

##### Connection

|                    |   |
|--------------------|---|
| Number of contacts | 3 |
|--------------------|---|

##### Equipment

|                               |     |
|-------------------------------|-----|
| Number of NO contacts         | 3   |
| Number of NC contacts         | 0   |
| With switch for manual switch | Yes |

##### Connection

|                                  |                        |
|----------------------------------|------------------------|
| Cross-section flexible conductor | 1 - 6 mm <sup>2</sup>  |
| Cross-section rigid conductor    | 1 - 10 mm <sup>2</sup> |

##### Installation, mounting

|                           |                |
|---------------------------|----------------|
| Nominal tightening torque | 1.20 - 1.20 Nm |
|---------------------------|----------------|

##### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|