



ETC325

### Night & Day Contactor 25A, 3NO, 230V~50Hz

#### Technical Features

##### Connection

Type of contacts	3NO
------------------	-----

##### Electric current

Rated current	25 A
---------------	------

##### Capacity

Number of modules	2
-------------------	---

##### Frequency

Frequency	50 - 50 Hz
-----------	------------

##### Voltage

Rated impulse withstand voltage Uimp	4000 V
Rated insulation voltage Ui	440 V
Rated operational voltage Ue	400 - 400 V
Command voltage AC	230 - 230 V
Command voltage DC	0 - 0 V

##### Use conditions

Operating temperature	-10 - 50 °C
-----------------------	-------------

##### Use

Category of use	AC-7a/AC-7b
-----------------	-------------

##### Use conditions

Storage/transport temperature	-40 - 80 °C
-------------------------------	-------------

##### Endurance

Number of mechanical operations	100000
Electric endurance in number of cycles	30000

##### Power

Total power loss under IN	6 W
Inrush power absorbed	21 VA

##### Dimensions

Height	83 mm
Width	35.75 mm
Depth	64 mm

##### Connection

Number of contacts	3
--------------------	---

##### Equipment

Number of NO contacts	3
Number of NC contacts	0
With switch for manual switch	Yes

##### Connection

Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1 - 10 mm <sup>2</sup>

##### Installation, mounting

Nominal tightening torque	1.20 - 1.20 Nm
---------------------------	----------------

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes