



52046089

Mains adapter frame, Q.1, p. white velvety

Technical Features

Voltage

Operating voltage	24 - 24 V
Input voltage	100 - 240 V
Output voltage	24 - 24 V

Materials

Colour	Polar white
RAL code	9010
Surface finish	Velvety

Dimensions

Height	80.50 mm
Width	80.50 mm
Depth	42 mm

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-5 - 40 °C
-----------------------	------------

Texts

Installation mode	Centre plate for plug-in fixing
Type of connection	With screw terminals

Suitable for

Q.x	
-----	--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes