



WBSCKSV1-MB

Silhouette 40A 2 pole Cooker Switch MB

Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Materials

Colour	Black
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished

Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	117 x 77 mm
Built-in depth	22 mm

Safety

Ingress Protection (IP) class	IP2X
-------------------------------	------

Electric current

Rated current	40 A
---------------	------

Texts

Installation mode	For screw fastening
Type of connection	With screw terminals
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-pole off

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes