



WBSCKSV1-MW

Silhouette 40A 2 pole Cooker Switch MW

Technical Features

Installation, mounting

Mounting on Flush mounting

Materials

Colour White

Surface finish Matt

Material Polycarbonate (PC)

Treatment Varnished

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 117 x 77 mm

Built-in depth 22 mm

Safety

Ingress Protection (IP) class IP2X

Electric current

Rated current 40 A

Texts

Installation mode For screw fastening

Type of connection With screw terminals

Lighting Without lighting (cannot be illuminated)

Switch mode 2-pole off

Sustainability

RoHS conform Yes