



WBSCKSV1-MW

**Silhouette 40A 2 pole Cooker Switch MW**

**Technical Features**

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Materials**

Colour	White
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished

**Identification**

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Controls and indicators**

Number of buttons	1
-------------------	---

**Dimensions**

Dimensions	117 x 77 mm
Built-in depth	22 mm

**Safety**

Ingress Protection (IP) class	IP2X
-------------------------------	------

**Electric current**

Rated current	40 A
---------------	------

**Texts**

Installation mode	For screw fastening
Type of connection	With screw terminals
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-pole off

**Sustainability**

RoHS conform	Yes
--------------	-----