



29452089



Extension unit insert f. uni rot. dim. comf., soft-lock., R.classic, pw gl.

Technical Features

Voltage

Operating voltage 230 - 230 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour Polar white

RAL code 9010

Material Metal
Plastic

Dimensions

Diameter axis 4 mm

Built-in depth 24 mm

Height 71 mm

Width 71 mm

Depth 45 mm

Architecture

Control/operation element Push & rotative switch

Power

Power consumption standby 0.30 W

Texts

Voltage Voltage test possible without dismantling

Installation mode With spreader claws

Type of connection With plug-in terminals

Equipment

Substation input No

Sustainability

REACH-SVHC free Yes

RoHS conform Yes