



47157004

## Schuko socket outlet K.5 Stainless steel metal matt finish

### Technical Features

#### Electric current

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

#### Voltage

|                 |             |
|-----------------|-------------|
| Rated voltage   | 250 V       |
| Nominal voltage | 250 - 250 V |

#### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

#### Materials

|                |                 |
|----------------|-----------------|
| Colour         | Stainless steel |
| RAL code       | 9022            |
| Surface finish | Matt            |
| Material       | Metal           |
|                | Stainless steel |

#### Dimensions

|                                    |       |
|------------------------------------|-------|
| Height                             | 71 mm |
| Width                              | 71 mm |
| Number of units                    | 1     |
| Built-in depth flush-mounted boxes | 31 mm |
| Built-in depth                     | 32 mm |

#### Connection

|                     |            |
|---------------------|------------|
| Connector/plug type | Plug clamp |
|---------------------|------------|

#### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

#### Connectivity

|                    |                    |
|--------------------|--------------------|
| Type of connection | Plug-in connection |
| Mounting type      | Screw mounting     |
|                    | Claw mounting      |

#### Equipment

|                                   |        |
|-----------------------------------|--------|
| Connector/plug type socket outlet | SCHUKO |
| Rotated central insert            | No     |
| With hinged lid                   | No     |
| With round protective earth pin   | No     |
| With signal lamp                  | No     |
| With lock                         | No     |

#### Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

#### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

#### Safety

|                                  |      |
|----------------------------------|------|
| With enhanced contact protection | No   |
| Impact resistance IK             | IK07 |
| Ingress Protection (IP) class    | IP20 |

#### Functions

|                           |    |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting    | No |

#### Texts

|         |                     |
|---------|---------------------|
| Imprint | Without imprint     |
| Cover   | Central cover plate |

Product Datasheet

47157004

|                    |                                     |
|--------------------|-------------------------------------|
| Texts              |                                     |
| Protection         | Without enhanced contact protection |
| Type of connection | With plug-in terminals              |

|              |  |
|--------------|--|
| Suitable for |  |
| K.x          |  |

|                |     |
|----------------|-----|
| Sustainability |     |
| Halogen free   | Yes |
| RoHS conform   | Yes |