



47157006

Schuko socket outlet K.1 anthracite matt lacquered

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Rated current	16 A
---------------	------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Anthracite
RAL code	7021
Surface finish	Matt
Material	Thermoplastic
Treatment	Varnished

Dimensions

Height	71 mm
Width	71 mm
Number of units	1
Built-in depth flush-mounted boxes	31 mm
Built-in depth	32 mm

Connection

Connector/plug type	Plug-in terminal
---------------------	------------------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting Claw mounting

Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	1
-------------------	---

Safety

With enhanced contact protection	No
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Cover	Central cover plate
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals

Suitable for

K.x
