



SPV040

Cartridge T2 1P photovoltaic +/- for SPV340

Technical Features

Capacity

Number of modules	1
-------------------	---

Voltage

Rated operational voltage U_e	1000 - 1000 V
Continuous operating voltage U_c according to IEC 61643-1	585 V
Voltage protection level U_p according to IEC 61643-1	1.90 kV
Voltage protection level U_p L-PE/N-PE according to IEC 61643-11	1.90 kV
Voltage level U_p L-N/PEN IEC 61643-11	1900 V

Electric current

Nominal discharge current I_n 8 - 20 μ s L-N(PEN)/N-PE IEC 61643	15 kA
Max. discharge (I_{max}) L-N(PEN)/ N-PE	40 kA

Dimensions

Height	52.40 mm
Width	17.50 mm
Depth	55.4 mm

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Network configuration

Network type	DC
--------------	----

Equipment

With remote signalling contact	No
--------------------------------	----

Standards

Requirement class IEC 61643	T2
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	3 - 3 Nm
---------------------------	----------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes