



85121101



**Universal Switch Insert 1gang, supporting ring round**

**Technical Features**

**Voltage**

Operating voltage 230 - 230 V

**Controls and indicators**

Applicable with movement sensor Yes

**Lighting**

LED lamp power 250 W

**Frequency**

Frequency 50 - 60 Hz

**Functions**

leading edge dimmer Yes

trailing edge dimmer Yes

**Lighting**

Dimmable 230 V LED lamp 3 - 250 W

**Power**

Power consumption standby 0.30 W

**Capacity**

Number of modules 0

**Use conditions**

Operating temperature -5 - 45 °C

**Dimensions**

Built-in depth 32 mm

**Texts**

Dimming principle Automatic setting of load-dependent switching principle (autodetect process)

Extension unit input With extension unit input for push-button (NO contact), single-surface operation and motion detector extension unit

Fuse Short-circuit and overload-proof (electronic fuse)

Installation mode With spreader claws

Type of connection With screw terminals

**Sustainability**

RoHS conform Yes