



CZ001

**Auxiliary contact for RCCB 2(1C+1O) 6A 240V AC**

**Technical Features**

**Electric current**

Rated current	6 A
---------------	-----

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Capacity**

Number of modules	1
-------------------	---

**Connection**

Cross-section flexible conductor	4 mm <sup>2</sup>
Cross-section rigid conductor	6 mm <sup>2</sup>

**Voltage**

Rated insulation voltage U <sub>i</sub>	500 V
Type voltage supply	AC

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Endurance**

Number of mechanical operations	12000
---------------------------------	-------

**Use conditions**

Operating temperature	-25 - 60 °C
-----------------------	-------------

**Endurance**

Electric endurance in number of cycles	6000
--	------

**Use conditions**

Storage/transport temperature	-40 - 80 °C
-------------------------------	-------------

**Power**

Total power loss under I <sub>N</sub>	0.10 W
---------------------------------------	--------

**Dimensions**

Width	18 mm
-------	-------

**Equipment**

Number of INV contacts	0
Number of NC contacts	1

**Sustainability**

RoHS conform	Yes
--------------	-----