



WGML111EAS

10A 1G press switch mark "exit";as

Technical Features

<b>Electric current</b>	
Switching current	10 A

<b>Voltage</b>	
Rated voltage	250 V

<b>Architecture</b>	
Control/operation element	Single rocker

<b>Materials</b>	
Colour	Aurora silver
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished
Transparent	No

<b>Dimensions</b>	
Height	86 mm
Width	86 mm
Depth	25 mm
Built-in depth flush-mounted boxes	35 mm

<b>Controls and indicators</b>	
Number of buttons	1

<b>Connectivity</b>	
Type of connection	Screw terminal

<b>Safety</b>	
Ingress Protection (IP) class	IP20

<b>Accessories</b>	
Has labelling field	No

<b>Suitable for</b>	
shark	

<b>Sustainability</b>	
RoHS conform	Yes