



CZ001

Auxiliary contact for RCCB 2(1C+1O) 6A 240V AC

Technical Features

Electric current

Rated current	6 A
---------------	-----

Connectivity

Type of connection	Screw terminal
Mounting type	Click mounting

Capacity

Number of modules	1
-------------------	---

Connection

Cross-section flexible conductor	4 mm ²
Cross-section rigid conductor	6 mm ²

Voltage

Rated insulation voltage Ui	500 V
Type voltage supply	AC

Frequency

Frequency	50 - 50 Hz
-----------	------------

Endurance

Number of mechanical operations	12000
---------------------------------	-------

Use conditions

Operating temperature	-25 - 60 °C
-----------------------	-------------

Endurance

Electric endurance in number of cycles	6000
--	------

Use conditions

Storage/transport temperature	-40 - 80 °C
-------------------------------	-------------

Power

Total power loss under IN	0.10 W
---------------------------	--------

Dimensions

Width	18 mm
-------	-------

Equipment

Number of INV contacts	0
Number of NC contacts	1

Sustainability

RoHS conform	Yes
--------------	-----