



LFS3004509016

**Trunking LFS made of steel 30x45mm in traffic white**

**Technical Features**

**Dimensions**

Height	30 mm
Width	45 mm
Length	2000 mm
Inner cross-section	970 - 970 mm <sup>2</sup>

**Capacity**

Max. number of cables (Ø11mm, 50% filled, without devices)	4
------------------------------------------------------------	---

**Materials**

Material	Steel
Treatment	Varnished
RAL code	9016
Colour	Traffic white

**Safety**

Impact resistance IK	IK08
Ingress Protection (IP) class	IP30

**Standards**

Suitable for functional integrity according to DIN4102-12	Yes
-----------------------------------------------------------	-----

**Use conditions**

Operating temperature	-5 - 90 °C
-----------------------	------------

**Connectivity**

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

**Equipment**

Number of partitions	0
Number of compartments	1 - 1
Number of pluggable partitions	0
Cable retaining clip included	No
With protective film	No

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes

**Illustrations | Drawings**

