



LFS3004509016

Trunking LFS made of steel 30x45mm in traffic white

Technical Features

Dimensions

| | |
|---------------------|---------------------------|
| Height | 30 mm |
| Width | 45 mm |
| Length | 2000 mm |
| Inner cross-section | 970 - 970 mm ² |

Capacity

| | |
|--|---|
| Max. number of cables (Ø11mm, 50% filled, without devices) | 4 |
|--|---|

Materials

| | |
|-----------|---------------|
| Material | Steel |
| Treatment | Varnished |
| RAL code | 9016 |
| Colour | Traffic white |

Safety

| | |
|-------------------------------|------|
| Impact resistance IK | IK08 |
| Ingress Protection (IP) class | IP30 |

Standards

| | |
|---|-----|
| Suitable for functional integrity according to DIN4102-12 | Yes |
|---|-----|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5 - 90 °C |
|-----------------------|------------|

Connectivity

| | |
|-------------------|--------------------------------|
| Trunking coupling | Couplers as separate reference |
|-------------------|--------------------------------|

Equipment

| | |
|--------------------------------|-------|
| Number of partitions | 0 |
| Number of compartments | 1 - 1 |
| Number of pluggable partitions | 0 |
| Cable retaining clip included | No |
| With protective film | No |

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |

Illustrations | Drawings

