



EG071



**Weekly time switch 1 channel, digital, 1 module**

**Technical Features**

**Voltage**

Rated operational voltage  $U_e$  230 - 230 V

**Frequency**

Frequency 50 - 50 Hz

**Power**

230 V incandescent and halogen lamp 1000 W

**Functions**

Power reserve in years 3 y  
 With network synchronisation No  
 With quartz synchronisation Yes  
 Number of function channels 1

**Equipment**

Accuracy per day 60 s  
 With impulse programme No  
 Number of channels 1

**Connection**

Type of contacts 1x changeover

**Settings**

Daily programme No  
 Weekly programme Yes  
 Annual programme No

**Use conditions**

Operating temperature -10 - 50 °C

**Connection**

Cross-section flexible conductor 1 - 4 mm<sup>2</sup>  
 Cross-section rigid conductor 1 - 4 mm<sup>2</sup>

**Texts**

Type of connection With screw terminals

**Dimensions**

Height 92 mm  
 Width 18 mm  
 Depth 64 mm

**Main electrical attributes**

Minimum interval between 2 switching times 1 min

**Capacity**

Number of modules 1