



EG071



### Weekly time switch 1 channel, 1 module

#### Technical Features

##### Voltage

Rated operational voltage $U_e$	230 - 230 V
---------------------------------	-------------

##### Frequency

Frequency	50 - 50 Hz
-----------	------------

##### Power

230 V incandescent and halogen lamp	1000 W
-------------------------------------	--------

##### Functions

Power reserve in years	3 y
With network synchronisation	No
With quartz synchronisation	Yes
Number of function channels	1

##### Equipment

Accuracy per day	60 s
With impulse programme	No
Number of channels	1

##### Connection

Type of contacts	1x changeover
------------------	---------------

##### Settings

Daily programme	No
Weekly programme	Yes
Annual programme	No

##### Use conditions

Operating temperature	-10 - 50 °C
-----------------------	-------------

##### Connection

Cross-section flexible conductor	1 - 4 mm <sup>2</sup>
Cross-section rigid conductor	1 - 4 mm <sup>2</sup>

##### Texts

Type of connection	With screw terminals
--------------------	----------------------

##### Dimensions

Height	92 mm
Width	18 mm
Depth	64 mm

##### Main electrical attributes

Minimum interval between 2 switching times	1 min
--	-------

##### Capacity

Number of modules	1
-------------------	---