



WGDL121NB

16AX 2G 1W switch;nb

Technical Features

Electric current

| | |
|-------------------|------|
| Switching current | 16 A |
|-------------------|------|

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Materials

| | |
|----------------|--------------------|
| Colour | Bronze |
| Surface finish | Matt |
| Material | Polycarbonate (PC) |
| Treatment | Varnished |

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 2 |
|-------------------|---|

Dimensions

| | |
|------------------------------------|------------|
| Dimensions | 86 x 86 mm |
| Built-in depth flush-mounted boxes | 35 mm |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Architecture

| | |
|---------------------------|---------------|
| Control/operation element | Double rocker |
|---------------------------|---------------|

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Texts

| | |
|-------------|-------|
| Switch mode | 1-way |
|-------------|-------|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |