



WPPS22

10AX 2 Gang 2 Way Wall Switch

Technical Features

Electric current

Switching current 10 A

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Materials

Colour Grey

Surface finish Glossy

Material Steel

Treatment Epoxy

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 2

Dimensions

Dimensions 86 x 86 mm

Built-in depth 10.80 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Double rocker

Electric current

Rated current 10 A

Texts

Installation mode For flush-mounted and hollow wall mounting

Lighting With control LED for ON

Switch mode 2-way

Sustainability

REACH-SVHC free Yes

RoHS conform Yes