



WXF423N

**Triple socket for trunking gallery 2P+E 16A night**

**Technical Features**

**Electric current**

Rated current 16 A

**Use conditions**

Operating temperature -10 - 35 °C

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Jet black

RAL code 9005

Surface finish Satin finish

Material Polycarbonate (PC)

Treatment Varnished

**Dimensions**

Height 42.50 mm

Width 135 mm

Number of units 3

Built-in depth flush-mounted boxes 50 mm

**Installation, mounting**

Mounting on Wall duct

**Connectivity**

Mounting type Click mounting  
Snap-on mounting

**Equipment**

Connector/plug type socket outlet French norm NF

Rotated central insert Yes

With hinged lid No

With round protective earth pin Yes

With signal lamp No

**Accessories**

Has labelling field No

**Capacity**

Number of modules 6

**Safety**

With enhanced contact protection Yes

Impact resistance IK IK07

Ingress Protection (IP) class IP20

**Functions**

With orientation lighting No

With function lighting No

**Identification**

With imprint No

**Texts**

Cover Complete housing

Protection Enhanced contact protection

**Suitable for**

Desk module / gallery

---

**Sustainability**

---

RoHS conform

Yes