



KB163P

**Insulated busbar 1P 63A prong 10mm<sup>2</sup> brown 13M**

**Technical Features**

**Electric current**

Rated current	63 A
---------------	------

**Architecture**

Number of poles	1
-----------------	---

**Dimensions**

Length	228 mm
--------	--------

**Voltage**

Rated impulse withstand voltage Uimp	4000 V
--------------------------------------	--------

Rated operational voltage Ue	415 - 415 V
------------------------------	-------------

**Connection**

Cross-section rigid conductor	10 mm <sup>2</sup>
-------------------------------	--------------------

Connector/plug type	Phase busbar with pin
---------------------	-----------------------

**Capacity**

Number of modules	13
-------------------	----

**Sustainability**

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----