



KB163P

Insulated busbar 1P 63A prong 10mm² brown 13M

Technical Features

Electric current

Rated current	63 A
---------------	------

Architecture

Number of poles	1
-----------------	---

Dimensions

Length	228 mm
--------	--------

Voltage

Rated impulse withstand voltage Uimp	4000 V
Rated operational voltage Ue	415 - 415 V

Connection

Cross-section rigid conductor	10 mm ²
Connector/plug type	Phase busbar with pin

Capacity

Number of modules	13
-------------------	----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes