



KB163P

Insulated busbar 1P 63A prong 10mm² brown 13M

Technical Features

Electric current

Rated current 63 A

Architecture

Number of poles 1

Dimensions

Length 228 mm

Voltage

Rated impulse withstand voltage Uimp 4000 V

Rated operational voltage Ue 415 - 415 V

Connection

Cross-section rigid conductor 10 mm²

Connector/plug type Phase busbar with pin

Capacity

Number of modules 13

Sustainability

REACH-SVHC free Yes

RoHS conform Yes