



WXF423V

Triple socket for trunking gallery 2P+E 16A green

Technical Features

Electric current

Rated current 16 A

Use conditions

Operating temperature -10 - 35 °C

Frequency

Frequency 50 - 60 Hz

Materials

Colour Green

RAL code 6024

Surface finish Glossy

Material Polycarbonate (PC)

Treatment Untreated

Dimensions

Height 42.50 mm

Width 135 mm

Number of units 3

Built-in depth flush-mounted boxes 50 mm

Installation, mounting

Mounting on Wall duct

Connectivity

Mounting type Click mounting
Snap-on mounting

Equipment

Connector/plug type socket outlet French norm NF

Rotated central insert Yes

With hinged lid No

With round protective earth pin Yes

With signal lamp No

Accessories

Has labelling field No

Capacity

Number of modules 6

Safety

With enhanced contact protection Yes

Impact resistance IK IK07

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

With function lighting No

Identification

With imprint No

Texts

Cover Complete housing

Protection Enhanced contact protection

Suitable for

Desk module / gallery

Sustainability

RoHS conform

Yes