



KB163PG

**Insulated busbar 1P 63A prong 10mm<sup>2</sup> brown 18M**

**Technical Features**

**Electric current**

Rated current 63 A

**Architecture**

Number of poles 1

**Dimensions**

Length 228 mm

**Voltage**

Rated impulse withstand voltage Uimp 4000 V

Rated operational voltage Ue 415 - 415 V

**Connection**

Cross-section rigid conductor 10 mm<sup>2</sup>

Connector/plug type Phase busbar with pin

**Capacity**

Number of modules 13

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes