



KDN463BZ

24mod Busbar 3P+N with 1mod space (L1N+L2N+L3N+1modspace)

Technical Features

Electric current

Rated current 63 A

Architecture

Number of poles 4

Dimensions

Length 425 mm

Voltage

Rated impulse withstand voltage U_{imp} 4000 V

Rated operational voltage U_e 230 - 400 V

Connection

Cross-section rigid conductor 10 mm²

Connector/plug type Phase busbar with fork

Capacity

Number of modules 24

Sustainability

REACH-SVHC free Yes

RoHS conform Yes