



WRDP84NPSW

20A Double Pole Switch with LED Indicator Polished Steel White Insert

Technical Features

Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Materials

|                |                 |
|----------------|-----------------|
| Colour         | Silver          |
| Surface finish | Glossy          |
| Material       | Stainless steel |

Identification

|                      |                                     |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

Dimensions

|                |            |
|----------------|------------|
| Dimensions     | 86 x 86 mm |
| Built-in depth | 20 mm      |

Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Architecture

|                           |               |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

Electric current

|               |      |
|---------------|------|
| Rated current | 20 A |
|---------------|------|

Texts

|             |                         |
|-------------|-------------------------|
| Lighting    | With control LED for ON |
| Switch mode | 2-pole                  |