

**APEX+ 18/24/24/12 Split-200A MCCB-DIN-X15**

**Technical Features**

**Connection**

Number of accessible phases

78

**Installation, mounting**

Mounting on

Surface mounting

**Electric current**

Rated current

200 A

Breaking and opening capacity ldm

0 kA

**Equipment**

With lock

Yes

Has mounting plate

No

Equipped with switch

No switch

Number of switches

0

Type of busbar chassis

Split chassis

**Capacity**

Number of modules

42

**Dimensions**

Height

1600 mm

Width

600 mm

Depth

200 mm

**Cover, door**

Door/cover is transparent

No

**Materials**

Material

Steel

RAL code

7035

Colour

Light grey

**Safety**

Protection class

Isolation class I

Impact resistance IK

IK05

Ingress Protection (IP) class

IP43

Locking type

3-point lever

**Architecture**

Number of poles

96

**Sustainability**

RoHS conform

Yes