Product Datasheet
WNE100B



WNE100B

cubyko Socket 2P+E screwless flush mounted white IP55

Technical Features

Electric current	
Rated current IN	16 A
Use conditions	
Operating temperature	-15 - 30 °C
Frequency	
Frequency	50 - 60 Hz
Materials	
Colour	White
RAL code	9010
Surface finish	Matt Satin finish
Material	Polycarbonate (PC) Polypropylene (PP)
Dimensions	
Height	75 mm
Width	75 mm
Depth	22.80 mm
Built-in depth flush-mounted boxes	40 mm
Installation, mounting	
Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal
Connectivity	
Type of connection	Plug-in connection
Mounting type	Screw mounting
Equipment	
Connector/plug type socket outlet	Earthing pin
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	Yes
With signal lamp	No
Cover, door	
Type of lid	Self-closing hinged cover, can be arrested in end position
Capacity	
Number of modules	2
Safety	
With enhanced contact protection	No
Impact resistance IK	IK07
Ingress Protection (IP) class	IP55
Functions	
With orientation lighting	No
Identification	
With imprint	No
Texts	
Cover	For covering of socket outlets
Protection	Without protective screen

Suitable for

cubyko

Sustainability

REACh-SVHC free	Yes